



Boiler cell assembly-cell constant 0.5, with J-box

Artikel-Nr.: **MH018S8SZ**

CHF Preis: Kontakt

Kein Versanddatum angezeigt

Mounting hardware for analog or digital sanitary style inductive conductivity sensors from 3700 family as well as for differential pH/ORP sensors pH/D and pure water conductivity sensors 3494.

316 Stainless Steel Sanitary 2-Inch Tee and Heavy Duty Clamp. For use with the sanitary style 3700-series inductive/electrodeless conductivity sensors.

Technische Daten

Anschlussgewinde:	2"
Bemerkungen:	Composition: stainless steel 2" tee piece heavy-duty clamp special cap EPDM compound gasket
Material:	Gasket: EPDM