



Ind. conductivity sensor, FEP, DN50 cone flange, 5m cable

Artikel-Nr.:

7MA22008BF

VERALTETER ARTIKEL

Dieser Artikel ist nicht mehr verfügbar.

Inductive conductivity sensors for use in industrial process water

Inductive conductivity sensor for use in industrial process water

Universal application thanks to wide measurement range and material variety

Concentration measurement of concentrated acid and lye

With integrated Pt100 for temperature compensation

Process connection: DN50 cone flange for installation in immersion and flow fittings

Technische Daten

Anschlussgewinde:	DN 50 Cone flange
Ansprechzeit:	thermometer 100 s T90
Betriebsbedingungen:	0 - 130 °C
Druckbereich:	10 bar
Eintauchtiefe:	96 mm
Gehäuse-Schutzklasse:	IP65
Gewicht:	approx. 1.2 kg
Kabellänge:	max. recommended 50 m
Lagerbedingungen:	-25 °C - 85 °C
Material:	FEP
Messbereich:	0,1 - 2500 mS/cm
Zellkonstante:	3.82 1/cm