



## pH combination electrode with temperature

Artikel-Nr.:

5193511

**VERALTETER ARTIKEL**

Dieser Artikel ist nicht mehr verfügbar.

Standard combination pH probe with a non-refillable gel reference and built-in temperature sensor. Contains fixed cable with BNC and 3.5 mm phone connectors compatible Hach One series meters.

### **Accurate**

You don't just need an answer, but the right one, and fast.

Optimized stabilization algorithms in Hach meter platforms eliminate operator guesswork and reduce inaccurate measurements. Many electrodes work specifically to deliver accurate results and the quickest response, even in challenging environments.

### **Easy to Use**

Now, more than ever, you're looking for new ways to stretch your dollar and resources. Skip studying complicated user manuals and spend your time measuring, thanks to Hach's innovative menu designs and simple keypads for truly intuitive operation.

### **Rugged and Durable**

Rely on Hach's durable measuring systems designed to withstand the rigors of outdoor testing and frequent use. Choose from the industry's toughest probes or non-glass electrodes for rugged, waterproof systems that deliver day after day.

### **Flexible**

Need to measure in both the lab and field? Hach offers efficiency with reliable, high-performance systems that easily move with you from the benchtop directly to the testing site. Measure the parameters you need today with the assurance you can expand in the future.

---

## Technische Daten

|                    |                                 |
|--------------------|---------------------------------|
| Connector (text):  | BNC and 3.5 mm Phone Connectors |
| Diaphragma:        | Glass frit                      |
| Durchmesser:       | 12.1 mm                         |
| Elektroden-Typ:    | Laboratory                      |
| Elektrolytlösung:  | Non-refillable gel              |
| Gewährleistung:    | 6 Monate                        |
| Kabellänge:        | 0.91 m                          |
| Länge:             | 152.5 mm                        |
| Material:          | Sensor Body: Epoxy              |
| Messbereich:       | 0 - 14 pH                       |
| Sensortyp:         | Glass                           |
| Temperaturbereich: | N/A N/A N/A                     |
| Thermistor:        | # (ATC)                         |