



## Stainless Steel 2 Inch Sanitary Clamp

**Artikel-Nr.:** 9H1132

CHF Preis: Kontakt

Kein Versanddatum angezeigt

2-inch Sanitary Clamp for 3455-series and PC/RC series sensors. Stainless Steel 316 L Material.

### Special Electrode Configurations

Sensors with rugged dome electrodes, easy-to-clean flat glass electrodes, and even HF (hydrofluoric acid) resistant glass electrodes are available for a wide variety of process solutions.

### Temperature Compensation Element Option

The PC-series combination pH sensors are available with or without a Pt 1000 ohm RTD temperature element. The RC-series combination ORP sensors are supplied without a temperature element.

### Versatile Mounting Styles

Sensors are available in three mounting styles: convertible, insertion, and sanitary.

### Full-Featured Plug and Play Hach sc Digital Controllers

There are no complicated wiring or set up procedures with any Hach sc controller. Just plug in any combination of Hach digital sensors and it's ready to use. One or multiple sensors can be connected to the sc controller family.